



### Standards

EN140: 1998 Mask Body  
EN14387: 2004 + A1: 2008 ABE1P3 R D  
CE 2797

### Efficiency

P3 >99,95% for 0,3 µ particulate  
At 1000 ppm:  
Cyclohexane (C<sub>6</sub>H<sub>12</sub>) > 70 minutes  
Chlorine (Cl<sub>2</sub>) > 20 minutes  
Hydrogen sulphide (H<sub>2</sub>S) > 40 minutes  
Hydrogen cyanide (HCN) > 25 minutes  
Sulphur dioxide (SO<sub>2</sub>) > 20 minutes

### Shelf Live

3 years (mask & filters) See storage conditions on Instructions for Use.  
Filters are re-usable and changeable.

### Material

- Mask:** Medical grade TPE Conforms to ISO 10993-10: 2010 for irritations. Mask body latex and silicone free, odour free. Valve Body in Nylon, Inhalation/Exhalation diaphragm in Silicone. 4 point adjustable elasticated head and neck strap with comfort pad in TPE.
- Gas Filters:** Activated carbon sealed into a ABS Shell.
- Particulate filters:** Mechanical type multi-layer HESPA Synthetic media with TPE flexible overmolded / encapsulated. Particulate filters are integrated with the carbon element.

### Production

United Kingdom



Code	Description	Quantity
SPR580 (S/M) SPR581 (M/L)	ABE1P3 Reusable Half Mask for Organic, Inorganic Gases and Dust	10 pcs. per box
SPR582	ABE1P3 Replacement filters	6 sets of 2 pcs. per box
SPM009	Elipse High efficiency Mask Carry Case (Belt holder)	10 sets per box

## Applications - Universal gases, dust, mist and fumes

### Type



### Protection

A organic gases and vapours with a boiling point above 65°C  
B inorganic gases and vapours (excluding carbon monoxide)  
E sulphur dioxide and other acidic gases and vapours  
P dust

